

Technical data sheet

Roof cable holder for slated roofs, Rd 8, A2

Item number: 5215439



- With Ø 5.5 mm drill hole and beading



A2 Stainless steel

Master data		
Item number	5215439	
Type	157 L-VA	
Description 1	Roof conductor holder	
Manufacturer	OBO	
Dimension	210mm	
Material	Stainless steel 1.4301	
Smallest sales unit	20	
Unit of quantity	Piece	
Weight	8 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,4318 kg CO2e / 1 Piece	

Dimensions		
	Length	212 mm
	Width	26 mm
	Height	32 mm

Technical data sheet

Roof cable holder for slated roofs, Rd 8, A2

Item number: 5215439



Technical data

Application	Roof surface
Conductor fastening type	With clip
Conductor diameter, max.	8
Conductor diameter, min.	8
Mounting type	Screw-on
Mounting height	32 mm
Fit	Rd 8 mm
ROHS-conformant	yes
Material of the holder	Rustproof steel (V2A)
Material of the support	Rustproof steel (V2A)