

Technical data sheet

165 MBG... roof cable holder for flat roofs, black, without concrete

Item number: 5218616



- Closed form with base
- With double conductor holder
- Without concrete
- Sleeve made of polyethylene, black, UV- and weather-resistant
- Base made of polyamide PA 6, black, UV- and weather-resistant
- Base can be used on almost all roofing felt systems (bitumen, PVC)
- Types 165 MBG...FO: Packed in foil bag

PE Polyethylene

Master data

Item number	5218616
Type	165 MBL-8-10
Description 1	Roof conductor holder
Description 2	without concrete filling
Manufacturer	OBO
Dimension	8mm
Colour	Black
Material	Polyethylene
Smallest sales unit	100
Unit of quantity	Piece
Weight	7.679 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,2526 kg CO2e / 1 Piece


Technical data sheet

165 MBG... roof cable holder for flat roofs, black, without concrete


Item number: 5218616



Dimensions



Length	133.5 mm
--------	----------



Technical data

Application	Flat roof
Conductor fastening type	With clip
Conductor diameter, max.	10
Conductor diameter, min.	8
Mounting type	Miscellaneous
Fit	Rd 8-10 mm
ROHS-conformant	yes
Material of the holder	Plastic
Material of the support	Plastic