


Technical data sheet

Vario quick connector Rd 8-10x16

Item number: 5311590



- For T, cross-over and parallel connections with adapter plates
- Quick mounting using an M10 x 30 bolt, made from rustproof stainless steel
- With sprung washer to DIN 137
- Corresponds to the requirements of VDE 0185-305 (IEC 62305)



A2 Stainless steel

Master data

Item number	5311590
Type	249 8-10X16 VA
Description 1	Quick connector
Description 2	Vario
Manufacturer	OBO
Dimension	50x40mm
Material	Stainless steel 1.4301
Smallest sales unit	10
Unit of quantity	Piece
Weight	14.958 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,9098 kg CO2e / 1 Piece


Technical data sheet

Vario quick connector Rd 8-10x16


Item number: 5311590



Dimensions



Length	50 mm
Width	40 mm
Dimension A	40 mm



Technical data

Type of fastening screw	Hexagonal bolt
Type of connector	Multipurpose connection clamp
Lightning current carrying capacity	H/100 kA
Suitable for connection	Round conductor Rd 8-10 / Rd 16
Short-circuit current (50 HZ)(1 s; $\leq 300^{\circ}\text{C}$)	7.9 kA
Fit	8-10x16 mm
ROHS-conformant	yes
Round conductor diameter, conductor 1, max.	10 mm
Round conductor diameter, conductor 1, min.	8 mm
Round conductor diameter, conductor 2, max.	16 mm
Round conductor diameter, conductor 2, min.	0 mm
Intermediate plate	no