


Technical data sheet

Cross-connector for flat conductor

Item number: 5314534



- Meets the requirements of VDE 0185-305-3 (IEC/EN 62305-3)
- Fit: Max FL 30 x FL 30
- Without adapter plate
- Mounted with 4 hexagonal bolts M6 x 20 (F)



St

Steel

FT

Hot-dip galvanised

Master data

Item number	5314534
Type	255 A-FL30 FT
Description 1	Cross-connectors
Description 2	no separator plate
Manufacturer	OBO
Dimension	30mm
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	20
Unit of quantity	Piece
Weight	10.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,2435 kg CO2e / 1 Piece

Technical data sheet

Cross-connector for flat conductor


Item number: 5314534



Dimensions



Dimension A	52 mm
Dimension B	52 mm



Technical data

Type of fastening screw	Hexagonal bolt
Type of connector	Cross-connectors
Lightning current carrying capacity	H/100 kA
Suitable for connection	Flat conductor FI 30 / FI 30
Fit	max. FL30 mm
Intermediate plate	no