


Technical data sheet

DIN cross-connector for flat conductor A4

Item number: 5314659



- Meets the requirements of VDE 0185-305-3 (IEC/EN 62305-3)
- Fit: Max. FL 30 x FL 30
- Without adapter plate
- Mounted with 4 hexagonal bolts M8 x 25 and 4 hexagonal nuts M8



A4 Stainless steel

Master data

Item number	5314659
Type	256 A-DIN 30 V4A
Description 1	Cross-connectors
Description 2	no separator plate
Manufacturer	OBO
Dimension	30mm
Material	Stainless steel 1.4571
Smallest sales unit	10
Unit of quantity	Piece
Weight	26.4 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,1874 kg CO2e / 1 Piece

Technical data sheet

DIN cross-connector for flat conductor A4


Item number: 5314659



Dimensions



Dimension A	60 mm
Dimension B	60 mm



Technical data

Type of fastening screw	Hexagonal bolt
Type of connector	Cross-connectors
Lightning current carrying capacity	H/100 kA
Suitable for connection	Flat conductor FI 30 / FI 30
Fit	max. FL30 mm
Intermediate plate	no