


Technical data sheet

Cover clip for WDK trunking, trunking width 170 mm

Item number: 6023541



Cover clip for better and easier laying of lines in the WDK trunking. The cover fixing device can be moved along the entire length of the trunking. The cover clip is locked on one side and moved forward. This provides a 30° opening, meaning that cable routing is very simple. From trunking widths of 110 mm, the cover clips can also be used as a mounting aid.




PVC Polyvinylchloride

Master data

Item number	6023541
Type	2370 170
Description 1	Cover fixing device
Manufacturer	OBO
Dimension	170mm
Colour	Light grey; RAL 7035
Material	Polyvinylchloride
Smallest sales unit	20
Unit of quantity	Piece
Weight	3.3 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1057 kg CO2e / 1 Piece

Dimensions



Length	36 mm
Width	156.7 mm
Dimension a	156.7 mm
Dimension b	36 mm

Technical data sheet

Cover clip for WDK trunking, trunking width 170 mm

Item number: 6023541



Technical data

Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
With equipotential bonding	no
Cover width	170 mm
ROHS-conformant	yes
Protection rating	IP30
Protection rating IK code	IK04
Self-extinguishing	yes
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C