

# Technical data sheet

## Bend, angle-adjustable, 60 A2

Item number: 6037154



Angle-adjustable bend for the creation of a horizontal branch, fitting for lock and screw-on cable trays of side height 60 mm. Adjustable angle 0–90°. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used indoors and outdoors. Fastening material must be ordered separately.



|    |                 |
|----|-----------------|
| A2 | Stainless steel |
| 2B | Bright, treated |

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 6037154                  |
| Type                               | RB W 620 A2              |
| Description 1                      | Adjustable bend          |
| Description 2                      | horizontal               |
| Manufacturer                       | OBO                      |
| Dimension                          | 60x200                   |
| Colour                             | stainless steel          |
| Material                           | Stainless steel 1.4301   |
| Surface                            | Bright, treated          |
| Surface standard                   |                          |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 74.1 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 7,4353 kg CO2e / 1 Piece |


# Technical data sheet

Bend, angle-adjustable, 60 A2

Item number: 6037154



## Dimensions



|                 |        |
|-----------------|--------|
| Width           | 200 mm |
| Height          | 60 mm  |
| Plate thickness | 1 mm   |
| Dimension B     | 200 mm |
| Dimension L     | 522 mm |

## Technical data

|                                         |                          |
|-----------------------------------------|--------------------------|
| Bend (angle)                            | Adjustable               |
| Connector version                       | Integrated connector     |
| Type                                    | Adjustable bend_complete |
| Maintain electrical functions           | no                       |
| Material thickness, floor plate         | 1 mm                     |
| With cover                              | no                       |
| Mounting perforation in base            | yes                      |
| NATO hole pattern                       | no                       |
| Change of direction                     | Horizontal               |
| ROHS-conformant                         | yes                      |
| Rustproof steel, pickled                | no                       |
| Side perforation                        | yes                      |
| Permitted temperature range, max.       | 120 °C                   |
| Permitted temperature range, min.       | -20 °C                   |
| Wide-span version                       | no                       |
| Type of connector, cable support system | screwed/clamped          |
| Recommended quantity of bolts           | 12 St.                   |
| Rail thickness                          | 1.25 mm                  |