


Technical data sheet

Cover, angle-adjustable bend A4

Item number: 6037578



Cover for angle-adjustable bend fitting for lockable and screw-on cable trays in indoor and outdoor areas, to protect cables against damage and soiling. Fastening with pre-mounted sash locks and through attachment of the section cover. Suitable for all side heights.



A4	Stainless steel
2B	Bright, treated

Master data

Item number	6037578
Type	RBD W 400 A4
Description 1	Cover
Description 2	for bend, adjustable
Manufacturer	OBO
Dimension	B400mm
Colour	stainless steel
Material	Stainless steel 1.4571
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	135 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	13,0115 kg CO2e / 1 Piece


Technical data sheet

Cover, angle-adjustable bend A4

Item number: 6037578



Dimensions



Width	400 mm
Plate thickness	1 mm
Dimension B	400 mm

Technical data

Bend (angle)	Adjustable
Number of turn buckles	2 St.
Fastening type	Sash lock
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Change of direction	Horizontal
ROHS-conformant	yes
Rustproof steel, pickled	no
Hinged	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C