

Technical data sheet

Barrier strip 135 DD

Item number: 6062338



Barrier strip for separation of cables of different voltages or functions.



St

Steel

DD

Strip galvanised zinc/aluminium, Double Dip

Master data

Item number	6062338
Type	TSG 135 DD
Description 1	Barrier strip
Description 2	for cable support systems
Manufacturer	OBO
Dimension	135x2995
Colour	zinc
Material	Steel
Surface	Strip galvanised zinc/aluminium, Double Dip
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	100 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	2,2686 kg CO2e / 1 Meter


Technical data sheet

Barrier strip 135 DD


Item number: 6062338



Dimensions



Length	3,000 mm
Height	135 mm
Plate thickness	0.75 mm
Dimension H	135 mm
Dimension L	3,000 mm



Technical data

Version for	L profile
Fastening type	Screw-on
Fastening perforation (ETIM)	no
Maintain electrical functions	no
Suitable for mesh cable tray	yes
Suitable for cable ladder	yes
Suitable for cable tray	yes
Rustproof steel, pickled	no