

Technical data sheet

Partition GKH-TW53

Item number: 6114166



Wall and ceiling trunking, halogen-free, consisting of base and cover for mounting directly on the wall.
During installation, ensure that only halogen-free accessories and fastening materials are used.



PC/
ABS

Polycarbonate/Acrylnitrile-butadiene-styrene

Master data

Item number	6114166
Type	GKH-TW53
Description 1	Partition halogen-free
Description 2	for Rapid 45-2
Manufacturer	OBO
Dimension	2000x13x38
Colour	Pure white; RAL 9010
Material	Polycarbonate/Acrylnitrile-butadiene-styrene
Smallest sales unit	2
Unit of quantity	Metre
Weight	14.3 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	0,6368 kg CO2e / 1 Meter

Technical data sheet

Partition GKH-TW53

Item number: 6114166



Dimensions



Length	2,000 mm
Width	10 mm
Height	38 mm

Technical data

Version for	Single
Fastening type	Plug-in
Suitable for duct depth	53
Halogen-free	yes
ROHS-conformant	yes
Protection rating	IP40
Protection rating IK code	IK08
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-15 °C