

Technical data sheet

Deskbox DBK, 2 sockets, 2x RJ45 Cat. 6

Item number: 6116802



Foldable Deskbox with connection cable for fixed installation in a tabletop, housing made of brushed stainless steel with brush bar as cable outlet. Mounting is done via an installation opening 195 x 157 mm in the tabletop.

Equipped with:

- two black protective contact sockets of 60° plug-in direction, including 3.0 power cable with angular connector CEE 7/7.

- two data technology couplings RJ45 on RJ45, 1:1, Cat. 6 shielded.

Note: Can be used in tabletops of up to 50 mm thickness.


The ready-for-connection type DBK Deskbox is particularly suitable for the direct supply of workstations with energy, communication and data technology connections.

A2 Stainless steel

Master data

Item number	6116802
Type	DBK2-D3 D2S2K
Description 1	Deskbox, foldable
Description 2	for installation in table tops
Manufacturer	OBO
Dimension	210x167x68
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	178.8 kg
Weight unit	kg/100 pc.

Dimensions



Length 210 mm

Technical data sheet

Deskbox DBK, 2 sockets, 2x RJ45 Cat. 6

Item number: 6116802



Technical data

Number of audio connections	0
Number of CAT 5 connections	0
Number of CAT 5E connections	0
Number of CAT 6 connections	2
Number of USB connections	0
Number of VGA connections	0
Number of HDMI connections	0
Number of SCHUKO sockets	2
Version for	Installation
Extendable	no
Shape	Rectangular
Foldable	yes
Length of the supply cable	3 m
Surge protection	no