

Technical data sheet

Protective contact socket, 33°, double

Item number: 6119452



Pre-terminated socket unit with labelling panel, suitable for installation in Rapid 80 device installation trunking systems and in service poles.

Socket unit, consisting of:

- Mounting support, double, type 71MT2 45
- Protective contact socket, double, 33° connection direction, colour: See table
- Cover frame AR45, double, with labelling panel, type AR45-BF., colour: Pure white

For installation in Rapid 80 device installation trunking and ISS service poles.

Master data

Item number	6119452
Type	SDE-ORW D3RW2B
Description 1	Socket unit
Description 2	for double Modul 45
Manufacturer	OBO
Dimension	84x140x40mm
Colour	Pure white; RAL 9010
Smallest sales unit	2
Unit of quantity	Piece
Weight	12.9 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,6781 kg CO2e / 1 Piece


Technical data sheet

Protective contact socket, 33°, double

Item number: 6119452



Dimensions



Technical data

Cover	Complete housing
Closable	no
Connection type	Screwless terminal
Number of units	2
Number of modules (for modular construction)	0
Number of switchable sockets	0
Number of poles	2
Printed label/coding	Without printing
Version for	Double 0°
Surface version	Matt
Version for	SCHUKO
Ejection mechanism	no
Fastening type	Lock
Labelling panel	no
increased touch protection	yes
Error current protection	no
For more difficult conditions (according to VDE)	no
Halogen-free	yes
Insulated installation	no
Hinged cover	no
Warning light	no
With on/off switch	no
With fine-wire fuse	no
With functional lighting	no
With orientation lighting	no
Mounting type	Device installation duct
Nominal voltage	250 V
Nominal current	16 A
ROHS-conformant	yes
Protection rating	Other
Special power supply	Without special power supply
Socket version	Protective contact
Socket angle	33°

Technical data sheet

Protective contact socket, 33°, double

Item number: 6119452



Technical data

Transparent	no
Rotated central insert	yes
Surge protection	no