

Technical data sheet

Coupling SL KUP2050

Item number: 6132225



Trunking coupling for SL, SL-L and SL-T skirting trunking. For connecting the interfaces of the individual trunking covers. Easily attached using moulded snap-in hooks.



PVC Polyvinylchloride

Master data

Item number	6132225
Type	SL KUP2050 rws
Description 1	Coupling
Description 2	SL 20x50 9010
Manufacturer	OBO
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	0.4 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0141 kg CO2e / 1 Piece


Technical data sheet

Coupling SL KUP2050


Item number: 6132225



Dimensions



Length	24 mm
Height	52 mm



Technical data sheet

Coupling SL KUP2050

Item number: 6132225



Technical data

Decoration	Without
Cover sealing lip	Without
Halogen-free	no
ROHS-conformant	yes
Protection rating	IP40
Protection rating IK code	IK06
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C