

Technical data sheet

Internal corner SLL IE2050

Item number: 6132241



Internal corner as a fitting for changing the direction of the skirting trunking.
Internal corner for snapping on to the base to conceal cuts.



PVC Polyvinylchloride

Master data

Item number	6132241
Type	SLL IE2050 cws
Description 1	Internal corner
Description 2	SL-L 20x50 9001
Manufacturer	OBO
Colour	Cream; RAL 9001
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	1.06 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0344 kg CO2e / 1 Piece


Technical data sheet

Internal corner SLL IE2050

Item number: 6132241



Dimensions



Length	45 mm
Width	45 mm
Height	60 mm

Technical data

Version for	Hood fitting
Decoration	Without
Cover sealing lip	Without
Halogen-free	no
With carpet strip	no
Protection rating	IP40
Protection rating IK code	IK06
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Angle range, min.	90 mm