

Technical data sheet

End piece SL ESli20110

Item number: 6132300



End piece (left) as a fitting for the skirting trunking.
For a clean end to the trunking system. For attaching to the trunking ends.



PVC Polyvinylchloride

Master data

Item number	6132300
Type	SL ESli20110 rws
Description 1	End piece left
Description 2	SL 20x110 9010
Manufacturer	OBO
Colour	Pure white; RAL 9010
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	1.01 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0288 kg CO2e / 1 Piece


Technical data sheet

End piece SL ESli20110


Item number: 6132300



Dimensions



Length	22 mm
Width	18 mm
Height	112 mm



Technical data sheet

End piece SL ESli20110

Item number: 6132300



Technical data

Version for	Left
Decoration	Without
Cover sealing lip	Without
Halogen-free	no
With carpet strip	no
ROHS-conformant	yes
Protection rating	IP40
Protection rating IK code	IK06
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C
Pre-markings	no