

Technical data sheet

Service pole, type ISS70110

Item number: 6288940



ISS aluminium service pole with a 76.5 mm system opening.

Set consists of:

1 single-compartment pole with clamping fastening

Total length 3,315–3,480 mm

1 ceiling fastening with clamping device

1 aluminium cover

Length: 3,000 mm

The service pole is suitable for accepting front-locking accessory mounting boxes of the series 71GD... The installation of a partition of type GA-TW70 (6279711)

and the installation of the cover clip, type KL80A (6288640), are possible as an option.

The following accessories can be used, depending on the mounting situation.



Alu Aluminium

Master data

Item number	6288940
Type	ISS70110RW
Description 1	Service pole
Description 2	floor/ceiling
Manufacturer	OBO
Dimension	3000x110x70
Colour	Pure white; RAL 9010
Material	Aluminium
Smallest sales unit	1
Unit of quantity	Piece
Weight	750 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	98,1752 kg CO2e / 1 Piece

Item number: 6288940

Length	3,000 mm
Width	110 mm
Height	70 mm

Technical data sheet

Service pole, type ISS70110

Item number: 6288940



Technical data

Number of usable covers	1
Number of compartments	1 St.
Version for	Single-sided
Fastening type	Tension
Floor mounting	yes
Ceiling mounting	yes
Continuous profile	yes
Halogen-free	yes
Height compensation, max.	480 mm
Height compensation, min.	315 mm
Cable entry	Top/bottom
Cover width	76.5 mm
Changes according to location	no
ROHS-conformant	yes
Pole shape	Rectangular
Pole height, max.	3480 mm
Pole height, min.	3315 mm
Adjustable	yes
Pre-wired	no