

Technical data sheet

Service pole, type ISSOG70140

Item number: 6289088



ISS service pole, oval shape, aluminium, with a 76.5 mm system opening.

Set consists of:

1 single-compartment column with clamping attachment

Total length: 3,315–3,480 mm

1 single-compartment pole with clamping device

1 trunking installation profile

Length 3,000 mm

1 aluminium cover

Length: 3,000 mm

The area for device installation is suitable for accepting front-locking accessory mounting boxes of the series 71GD...

The following accessories can be used, depending on the mounting situation.



Alu	Aluminium
EL	Anodised

Master data

Item number	6289088
Type	ISSOG70140EL
Description 1	Service pole
Description 2	Floor/ceiling
Manufacturer	OBO
Dimension	3000x146x65
Colour	aluminium
Material	Aluminium
Surface	Anodised
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	700 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	93,3884 kg CO2e / 1 Piece


Technical data sheet

Service pole, type ISSOG70140

Item number: 6289088



Dimensions



Length	3,000 mm
Width	146 mm
Height	65 mm

Technical data

Number of usable covers	1
Number of compartments	1 St.
Version for	Single-sided
Fastening type	Tension
Floor mounting	yes
Ceiling mounting	yes
Continuous profile	yes
Halogen-free	yes
Height compensation, max.	480 mm
Height compensation, min.	315 mm
Cable entry	Top/bottom
Cover width	76.5 mm
Changes according to location	no
Pole shape	Oval
Pole height, max.	3480 mm
Pole height, min.	3315 mm
Adjustable	yes
Pre-wired	no