

Technical data sheet

Chuck jaw, heavy duty TKS ZL

Item number: 6355798



Heavy-duty chuck jaw with hexagonal nut for direct fastening of structures to steel girders.
The clamping range of the chuck jaw is limited to the maximum fastening thickness, 30 mm.



St	Steel
ZL	Zinc slat

Master data

Item number	6355798
Type	TKS-S-30 ZL
Description 1	Tensioning claw, heavy
Description 2	with combination nut
Manufacturer	OBO
Dimension	M12x75
Colour	zinc
Material	Steel
Surface	Zinc slat
Surface standard	
Smallest sales unit	10
Unit of quantity	Pair
Weight	82.8 kg
Weight unit	kg/100 pairs


Technical data sheet

Chuck jaw, heavy duty TKS ZL

Item number: 6355798



Dimensions



Height	30 mm
--------	-------

Technical data

F in kN	21 kN
Suitable for flange thickness, max.	30 mm
Suitable for flange thickness, min.	20 mm
Thread metric	12
ROHS-conformant	yes
Bolt	M12 x 75