

Technical data sheet

Chuck jaw, light duty TKS A2

Item number: 6355836



Chuck jaw with hexagonal nut for direct fastening of structures to steel girders. The clamping range of the chuck jaw is limited to the maximum fastening thickness of 36 mm.



A2 Stainless steel

Master data

Item number	6355836
Type	TKS-L36 M12 A2
Description 1	Tensioning claw, light
Manufacturer	OBO
Dimension	M12x80
Colour	stainless steel
Material	Stainless steel 1.4301
Smallest sales unit	25
Unit of quantity	Piece
Weight	36 kg
Weight unit	kg/100 pc.


Technical data sheet

Chuck jaw, light duty TKS A2

Item number: 6355836



Dimensions



Height	36 mm
--------	-------

Technical data

F in kN	10 kN
Suitable for flange thickness, max.	36 mm
Suitable for flange thickness, min.	16 mm
Thread metric	12
ROHS-conformant	yes
Bolt	M12 x 80