

Technical data sheet

Wall and support bracket MWA 12



Item number: 6424716

Chalfant Item Nb.



Light-duty wall and support bracket.
Including truss-head bolt M10 x 25 for fastening to
U supports.
Including truss-head screw M10 x 25 for fastening to
U supports.




St Steel

FS Strip galvanized

Master data

Type	MWA 12 11S FS
Manufacturer	OBO
Colour	zinc
Material	Steel
Surface	Strip-galvanized
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Units
Weight	15.86 kg
Weight unit	kg/100 pairs

Dimensions



Length	32.5 mm
Width	110 mm
Width	4 in
Height	53 mm
Height	2.09 in
Dimension A	32.5 mm
Dimension B	110 mm
Dimension H	53 mm

Technical data sheet

Wall and support bracket MWA 12




Item number: 6424716

Chalfant Item Nb.

Features/properties/dimensions

Version	Wall and support bracket
F in kN	1.2 kN
Maintain electrical functions	yes
Hole diameter	11 mm
Rustproof steel, pickled	no
Angle range, max.	90 mm
Angle range, min.	90 mm

Loads



Load diagram, bracket, type MWA 12

- 1 Bending of the bracket tip at permitted bracket load
- 2 Permitted bracket load in kN without man load
- Load curve with bracket lengths in mm