Technical data sheet

Head plate US 5 FT SOMY

Item number: 7193547



Head plate for mounting on US 5 supports. In combination with the US 5 support, suspended supports of any length can be created in situ. Also suitable for fixing vertical ladders, type SLM 50.

The head plate can be mounted to fixed lengths of the U support, type US 5. The spacer, type DSK 45, is used to install the head plate.

CE US5

St Steel

FT SO Hot-dip galvanised 85 µm

Master data


Item number	7193547
Type	KUS 5 FT SO
Description 1	Head plate
Description 2	for US 5 support
Manufacturer	OBO
Dimension	140x75x104
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised 85 µm
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	63 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,7297 kg CO2e / 1 Piece

Technical data sheet

Head plate US 5 FT SOMY

Item number: 7193547

Dimensions



Length	140 mm
Width	75 mm
Height	104 mm

Technical data

Version for	Screw head plate
Maintain electrical functions	no
Suitable for ceiling fastening	yes
Suitable for panel fastening	no
Suitable for profile shapes	U profile
ROHS-conformant	yes
Rustproof steel, pickled	no
Angle range, max.	90 mm
Angle range, min.	90 mm