

Technical data sheet

Metal strip clips, wide

Item number: 7203109



Metal strip clip in a smooth finish with ball lock. For high-temperature and weather-resistant fastening. Use spring chuck MBS-Z for tightening.

A2 Stainless steel

2B Bright, treated

Master data

Item number	7203109
Type	MBS 075 A2
Description 1	Strip clip
Manufacturer	OBO
Dimension	12x750
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	2.01 kg
Weight unit	kg/100 pc.

Dimensions

Length	750 mm
Width	12 mm
Height	6.5 mm
Dimension L	750 mm
Dimension t	0.25 mm

Technical data sheet

Metal strip clips, wide

Item number: 7203109



Technical data

Version for	Without toothing
Strip closure	Ball lock
Fastening type	Without
Labelling area	Without
Halogen-free	yes
Releasable lock	no
Max. Bundle diameter	105 mm
MIL approval	no
Mounting temperature, max.	50 °C
Min. mounting temperature	5 °C
Reflective	no
Permitted temperature range, max.	70 °C
Permitted temperature range, min.	-20 °C
Transparent	no
UL approval	no
UV-resistant	yes
VG approval	no