

Technical data sheet

UDHOME2 floor socket, with cord outlet, with floor covering recess, double protective contact socket, stainless steel



Square floor socket for use in dry-care cavity and screed floors in indoor areas. Installation housing with pre-marked insertion openings for pipes (M20/M25). Cover adjustable to top edge of floor covering using four height-adjustment supports. The minimum installation depth is 110 mm, the height-adjustment range 25 mm. Frame and cover made of stainless steel and visible in the floor covering. With 2 Modul 45® sockets in the mounting support and an optional data technology support for up to 2 data connection modules.



A2 Stainless steel

Master data


Item number	7368324
Type	UDHOME2 GV15V
Description 1	Floor socket
Description 2	2x protective contact socket
Manufacturer	OBO
Dimension	140x140x110
Material	Stainless steel
Smallest sales unit	1
Unit of quantity	Piece
Weight	230 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	12,8567 kg CO2e / 1 Piece

Technical data sheet


UDHOME2 floor socket, with cord outlet, with floor covering recess, double protective contact socket, stainless steel



Dimensions



Length	140 mm
Width	140 mm
Height	110 mm



Technical data

Number of installable devices	2
Cover version	Square
Cable outlet version	Swivellable cord outlet
Equipment	Double VDE socket
Floor covering protection frame	no
Floor care	Dry
Cover version	Floor covering recess
Application when used	6.101.1 Dry floor care
Application when unused	6.101.1 Dry floor care
Floor height, max.	135 mm
Floor height, min.	110 mm
Suitable for raised floor installation	yes
Suitable for screed-flush closed underfloor ducts	no
Suitable for screed-covered underfloor ducts	no
Suitable for cavity floor installation	yes
Suitable for wet care	no
Suitable for underfloor ducts	no
Device support to accept mounting boxes	no
With floor covering recess	yes
Nominal size for device installation units	2
Standard	EN 50085-2-2
Frame version	Floor covering contact edge

Technical data sheet

UDHOME2 floor socket, with cord outlet, with floor covering recess, double protective contact socket, stainless steel



Technical data

Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP40
Protection rating IK code	IK10
Heavy-duty version	no
Vertical load, large area	to 15,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE
Opening mechanism	Handle
Floor covering thickness	15 mm