


Technical data sheet

Trunking unit with blanking lid

Item number: 7403818



Ready-to-mount trunking unit for cable routing and device installation, consisting of a trunking base with two blanking covers. The scope of delivery contains two lid butt seals and one connector. For height adjustment, six height adjustment units are required. Load capacity up to a maximum of 5 kN. The trunking unit can be supplemented with an adjustable floor covering contact profile for screed limitation in areas of door frames and in front of radiator niches.



St

Steel

FS

Strip galvanised

Master data

Item number	7403818
Type	OKB U 25085 BD
Description 1	Flushfloor trunking unit
Description 2	with blanking lid
Manufacturer	OBO
Dimension	2000x273x85
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	1448.5 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	55,8728 kg CO2e / 1 Meter


Technical data sheet

Trunking unit with blanking lid

Item number: 7403818



Dimensions



Length	2,000 mm
Width	250 mm
Height	93 mm
Dimension h	85 mm

Technical data

Mounting opening cover	no
Number of compartments	2 St.
Floor plate	yes
Floor care	Dry
Cover fastening, locking	no
Seal installation option	no
Installation opening for on-floor tank	no
Decouplable	yes
Suitable for expansion joint	no
Mesh wall	no
Minimum screed height	93
With connection opening	no
With equipotential bonding	no
With separating retainer	no
With overhang	yes
Mounting opening	Without
Height-adjustment range, min.	0 mm
Removable cover	yes
Cross-section, draw a	4231 mm ²
Cross-section, draw b	7306 mm ²
Separating retainer fastening	stecken
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Separating retainer fastening	Plug