

# Technical data sheet

## Trunking unit, blank, height 60–110 mm

Item number: 7424422



Ready-to-mount trunking unit with three blanking lids for cable laying, consisting of the trunking base (floor trough with side and floor covering contact profiles) and trunking lid. Floor trough with holding straps for self-contacting mounting of separating retainers. The scope of delivery contains 6 height-adjustable fixing brackets, 6 screed anchors and lid butt seals (3x for nominal trunking widths of 200 and 300) or height-adjustable lid butt supports: 3x for nominal trunking width 400 and 6x for nominal trunking widths 500 and 600. Trunking lid screwed on for delivery.



St

Steel


FS

Strip galvanised

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 7424422                  |
| Type                               | OKA-W3006050             |
| Description 1                      | Flushfloor trunking unit |
| Description 2                      | blank                    |
| Manufacturer                       | OBO                      |
| Dimension                          | 2400x300x60              |
| Material                           | Steel                    |
| Surface                            | Strip galvanised         |
| Surface standard                   | DIN EN 10346             |
| Smallest sales unit                | 2.4                      |
| Unit of quantity                   | Metre                    |
| Weight                             | 1404.2 kg                |
| Weight unit                        | kg/100 m                 |
| CO2 Footprint (GWP) Cradle-to-Gate | 60,716 kg CO2e / 1 Meter |

### Dimensions



|        |          |
|--------|----------|
| Length | 2,400 mm |
| Width  | 300 mm   |

# Technical data sheet

Trunking unit, blank, height 60–110 mm

Item number: 7424422



## Technical data

|                                        |                      |
|----------------------------------------|----------------------|
| Mounting opening cover                 | no                   |
| Covers                                 | 3                    |
| Number of mounting openings            | 0                    |
| Number of insertable partitions        | 2                    |
| Number of planned flush-mount units    | 3                    |
| Number of compartments                 | 3 St.                |
| Mounting system fastening type         | Floor                |
| Floor plate                            | yes                  |
| Cover fastening, locking               | no                   |
| Seal installation option               | yes                  |
| Installation opening for on-floor tank | no                   |
| Decouplable                            | no                   |
| Suitable for expansion joint           | no                   |
| Mesh wall                              | no                   |
| Trunking height, max.                  | 110 mm               |
| Duct height, min.                      | 60 mm                |
| Cover material thickness               | 4                    |
| Minimum screed height                  | 60                   |
| With connection opening                | no                   |
| With equipotential bonding             | no                   |
| With separating retainer               | no                   |
| With overhang                          | yes                  |
| Mounting opening                       | Without              |
| Height-adjustment range, max.          | 110 mm               |
| Height-adjustment range, min.          | 60 mm                |
| Usable cross-section                   | 8100 mm <sup>2</sup> |
| Removable cover                        | yes                  |
| Separating retainer fastening          | rasten               |
| Separating retainer fastening          | Lock                 |