


Selection aid cable trays, screw-on

www.obo-bettermann.com | Customer Service Germany Tel.: +49 (0)2373 89-1700

Screw-on cable trays, side height 60 mm



MKS cable tray

Type	Width mm	Plate thickness mm	Item no.
MKS 610 FS	100	1	6055109
MKS 615 FS	150	1	6055141
MKS 620 FS	200	1	6055206
MKS 630 FS	300	1	6055303
MKS 640 FS	400	1	6055400
MKS 650 FS	500	1	6055508
MKS 660 FS	600	1	6055524


MKS 610 FT	100	1	6055532
MKS 615 FT	150	1	6055575
MKS 620 FT	200	1	6055575
MKS 630 FT	300	1	6055613
MKS 640 FT	400	1	6055664
MKS 650 FT	500	1	6055699
MKS 660 FT	600	1	6055710



Cover, unperforated

Type	Width mm	Item no.
DRLU 100 FS	100	6052103
DRLU 150 FS	150	6052153
DRLU 200 FS	200	6052210
DRLU 300 FS	300	6052307
DRLU 400 FS	400	6052405
DRLU 500 FS	500	6052512
DRLU 600 FS	600	6052609

DRLU 100 DD	100	6052643
DRLU 150 DD	150	6052647
DRLU 200 DD	200	6052650
DRLU 300 DD	300	6052656
DRLU 400 DD	400	6052662
DRLU 500 DD	500	6052668
DRLU 600 DD	600	6052674



Cable tray SKS

Type	Width mm	Plate thickness mm	Item no.
SKS 610 FS	100	1.5	6056105
SKS 615 FS	150	1.5	6056156
SKS 620 FS	200	1.5	6056202
SKS 630 FS	300	1.5	6056296
SKS 640 FS	400	1.5	6056407
SKS 650 FS	500	1.5	6056504
SKS 660 FS	600	1.5	6056601

SKS 610 FT	100	1.5	6056636
SKS 615 FT	150	1.5	6056644
SKS 620 FT	200	1.5	6056652
SKS 630 FT	300	1.5	6056679
SKS 640 FT	400	1.5	6056695
SKS 650 FT	500	1.5	6056717
SKS 660 FT	600	1.5	6056733



Cover with turn buckle

Type	Width mm	Item no.
DRL 100 FS	100	6052096
DRL 150 FS	150	6052150
DRL 200 FS	200	6052207
DRL 300 FS	300	6052304
DRL 400 FS	400	6052401
DRL 500 FS	500	6052509
DRL 600 FS	600	6052606


DRL 100 DD	100	6052703
DRL 150 DD	150	6052706
DRL 200 DD	200	6052709
DRL 300 DD	300	6052712
DRL 400 DD	400	6052715
DRL 500 DD	500	6052718
DRL 600 DD	600	6052724



Reducer and stop-end

Type	Width mm	Item no.
RWEB 610 FS	100	7109105
RWEB 615 FS	150	7109156
RWEB 620 FS	200	7109202
RWEB 630 FS	300	7109296
RWEB 640 FS	400	7109407
RWEB 650 FS	500	7109504
RWEB 660 FS	600	7109601

RWEB 610 DD	100	7106106
RWEB 615 DD	150	7106110
RWEB 620 DD	200	7106114
RWEB 630 DD	300	7106118
RWEB 640 DD	400	7106122
RWEB 650 DD	500	7106126
RWEB 660 DD	600	7106130



Bottom end plate

Type	Width mm	Item no.
BEB 100 FS	100	7083106
BEB 150 FS	150	7083157
BEB 200 FS	200	7083203
BEB 300 FS	300	7083300
BEB 400 FS	400	7083408
BEB 500 FS	500	7083505
BEB 600 FS	600	7083602

BEB 100 DD	100	7083618
BEB 150 DD	150	7083622
BEB 200 DD	200	7083626
BEB 300 DD	300	7083630
BEB 400 DD	400	7083634
BEB 500 DD	500	7083638
BEB 600 DD	600	7083642

Surfaces and areas of application:

FS Strip galvanisation, for use in internal areas

DD Double-dip galvanisation, for use in external areas

F Electrogalvanisation, for use in external areas

FT Hot-dip galvanisation, for use in external areas

V2A Stainless steel, rustproof

Light duty mounting system



US 3 suspended support

Type	Length mm	Plate thickness mm	Item no.
US 3 K 20 FT	200	2	6342351
US 3 K 30 FT	300	2	6342353
US 3 K 40 FT	400	2	6342355
US 3 K 50 FT	500	2	6342357
US 3 K 60 FT	600	2	6342359
US 3 K 70 FT	700	2	6342362



Wall and support bracket MWAM 12

Type	Width mm	Item no.
MWAM 12 11 FS	110	6424550
MWAM 12 21 FS	210	6424552
MWAM 12 31 FS	310	6424554
MWAM 12 41 FS	410	6424556



Spacer

Type	Item no.
DSK 25 FT	6416446



Hexagonal bolt

Type	Item no.
SKS 10x80 F	6418250

Medium-duty mounting system



US 5 suspended support

Type	Length mm	Plate thickness mm	Item no.
US 5 K 20 FT	200	2.5	6341527
US 5 K 30 FT	300	2.5	6341535
US 5 K 40 FT	400	2.5	6341543
US 5 K 50 FT	500	2.5	6341551
US 5 K 60 FT	600	2.5	6341578
US 5 K 70 FT	700	2.5	6341586



Wall and support bracket AW 15

Type	Width mm	Item no.
AW 15 11 FT	110	6420656
AW 15 16 FT	160	6420664
AW 15 21 FT	210	6420680
AW 15 31 FT	310	6420710
AW 15 41 FT	410	6420745
AW 15 51 FT	510	6420788
AW 15 61 FT	610	6420826



Spacer

Type	Item no.
DSK 45 FT	6416500



Hexagonal bolt

Type	Item no.
SKS 10x80 F	6418250
SKS 10x90 F	6418252
SKS 10x120 F	3160793



Truss-head bolt with combination nut

Type	Item no.
FRSB 6x12 F	6406122

Heavy duty mounting system



US 7 suspended support

Type	Length mm	Plate thickness mm	Item no.
US 7 K 20 FT	200	4	6339018
US 7 K 30 FT	300	4	6339034
US 7 K 40 FT	400	4	6339050
US 7 K 50 FT	500	4	6339077
US 7 K 60 FT	600	4	6339093
US 7 K 70 FT	700	4	6339115



Wall and support bracket AW 30

Type	Width mm	Item no.
AW 30 11 FT	110	6419704
AW 30 16 FT	160	6419712
AW 30 21 FT	210	6419720
AW 30 31 FT	310	6419747
AW 30 41 FT	410	6419763
AW 30 51 FT	510	6419798
AW 30 61 FT	610	6419828



Spacer

Type	Item no.
DSK 61 FT	6416519



Hexagonal bolt


Type	Item no.
SKS 12x80 F	6418287
SKS 12x100 F	6418295
SKS 12x110 F	6418317
SKS 12x130 F	6408478



Protective cap

Type	Item no.
US 3 KS OR	6338458
US 5 KS OR	6338462
US 7 KS OR	6338497


Universal fittings and accessories for side height 60 mm



Bend, angle-adjustable

Type	Width mm	Item no.
RB W 610 FS	100	6037100
RB W 615 FS	150	6037102
RB W 620 FS	200	6037104
RB W 630 FS	300	6037106
RB W 640 FS	400	6037108
RB W 650 FS	500	6037110
RB W 660 FS	600	6037112


RB W 610 FT	100	6037120
RB W 615 FT	150	6037122
RB W 620 FT	200	6037124
RB W 630 FT	300	6037126
RB W 640 FT	400	6037128
RB W 650 FT	500	6037130
RB W 660 FT	600	6037132



45° bend

Type	Width mm	Item no.
RB 45 610 FS	100	6036100
RB 45 615 FS	150	6036102
RB 45 620 FS	200	6036104
RB 45 630 FS	300	6036106
RB 45 640 FS	400	6036108
RB 45 650 FS	500	6036110
RB 45 660 FS	600	6036112


RB 45 610 FT	100	6036130
RB 45 615 FT	150	6036132
RB 45 620 FT	200	6036134
RB 45 630 FT	300	6036136
RB 45 640 FT	400	6036138
RB 45 650 FT	500	6036140
RB 45 660 FT	600	6036142



90° bend

Type	Width mm	Item no.
RB 90 610 FS	100	6036560
RB 90 615 FS	150	6036562
RB 90 620 FS	200	6036564
RB 90 630 FS	300	6036566
RB 90 640 FS	400	6036568
RB 90 650 FS	500	6036570
RB 90 660 FS	600	6036572


RB 90 610 FT	100	6036590
RB 90 615 FT	150	6036592
RB 90 620 FT	200	6036594
RB 90 630 FT	300	6036596
RB 90 640 FT	400	6036598
RB 90 650 FT	500	6036600
RB 90 660 FT	600	6036602



Mounting/branch piece

Type	Width mm	Item no.
RAA 610 FS	100	6042111
RAA 615 FS	150	6042113
RAA 620 FS	200	6042115
RAA 630 FS	300	6042117
RAA 640 FS	400	6042119
RAA 650 FS	500	6042121
RAA 660 FS	600	6042123


RAA 610 FT	100	6042211
RAA 615 FT	150	6042213
RAA 620 FT	200	6042215
RAA 630 FT	300	6042217
RAA 640 FT	400	6042219
RAA 650 FT	500	6042221
RAA 660 FT	600	6042223



T branch piece

Type	Width mm	Item no.
RT 610 FS	100	6038100
RT 615 FS	150	6038102
RT 620 FS	200	6038104
RT 630 FS	300	6038106
RT 640 FS	400	6038108
RT 650 FS	500	6038110
RT 660 FS	600	6038112

RT 610 FT	100	6038130
RT 615 FT	150	6038132
RT 620 FT	200	6038134
RT 630 FT	300	6038136
RT 640 FT	400	6038138
RT 650 FT	500	6038140
RT 660 FT	600	6038142



Intersection

Type	Width mm	Item no.
RK 610 FS	100	7027311
RK 620 FS	200	7027313
RK 630 FS	300	7027315
RK 640 FS	400	7027317
RK 650 FS	500	7027319
RK 660 FS	600	7027321

RK 610 FT	100	7027411
RK 620 FT	200	7027413
RK 630 FT	300	7027415
RK 640 FT	400	7027417
RK 650 FT	500	7027419
RK 660 FT	600	7027421



Cover for bend, angle-adjustable

Type	Width mm	Item no.
RBD W 100 FS	100	6037500
RBD W 150 FS	150	6037502
RBD W 200 FS	200	6037504
RBD W 300 FS	300	6037506
RBD W 400 FS	400	6037508
RBD W 500 FS	500	6037510
RBD W 600 FS	600	6037512


RBD W 100 DD	100	6037540
RBD W 150 DD	150	6037542
RBD W 200 DD	200	6037544
RBD W 300 DD	300	6037546
RBD W 400 DD	400	6037548
RBD W 500 DD	500	6037550
RBD W 600 DD	600	6037552



Cover for 45° bend

Type	Width mm	Item no.
RBD 45 100 FS	100	6036400
RBD 45 150 FS	150	6036402
RBD 45 200 FS	200	6036404
RBD 45 300 FS	300	6036407
RBD 45 400 FS	400	6036408
RBD 45 500 FS	500	6036410
RBD 45 600 FS	600	6036412

RBD 45 100 DD	100	6036450
RBD 45 150 DD	150	6036452
RBD 45 200 DD	200	6036454
RBD 45 300 DD	300	6036456
RBD 45 400 DD	400	6036458
RBD 45 500 DD	500	6036460
RBD 45 600 DD	600	6036462



Cover for 90° bend

Type	Width mm	Item no.
RBD 90 100 FS	100	6036900
RBD 90 150 FS	150	6036902
RBD 90 200 FS	200	6036904
RBD 90 300 FS	300	6036906
RBD 90 400 FS	400	6036908
RBD 90 500 FS	500	6036910
RBD 90 600 FS	600	6036912


RBD 90 100 DD	100	6036950
RBD 90 150 DD	150	6036952
RBD 90 200 DD	200	6036954
RBD 90 300 DD	300	6036956
RBD 90 400 DD	400	6036958
RBD 90 500 DD	500	6036960
RBD 90 600 DD	600	6036962



Cover for add-on tee

Type	Width mm	Item no.
RAAD 100 FS	100	6042401
RAAD 150 FS	150	6042403
RAAD 200 FS	200	6042405
RAAD 300 FS	300	6042407
RAAD 400 FS	400	6042409
RAAD 500 FS	500	6042411
RAAD 600 FS	600	6042413

RAAD 100 DD	100	6042431
RAAD 150 DD	150	6042433
RAAD 200 DD	200	6042435
RAAD 300 DD	300	6042437
RAAD 400 DD	400	6042439
RAAD 500 DD	500	6042441
RAAD 600 DD	600	6042443



Cover for T branch piece

Type	Width mm	Item no.
RTD 100 FS	100	6038600
RTD 150 FS	150	6038602
RTD 200 FS	200	6038604
RTD 300 FS	300	6038606
RTD 400 FS	400	6038608
RTD 500 FS	500	6038610
RTD 600 FS	600	6038612

RTD 100 DD	100	6038640
RTD 150 DD	150	6038642
RTD 200 DD	200	6038644
RTD 300 DD	300	6038646
RTD 400 DD	400	6038648
RTD 500 DD	500	6038650
RTD 600 DD	600	6038652



Cover for cross-over

Type	Width mm	Item no.
RKD 100 FS	100	7027800
RKD 200 FS	200	7027802
RKD 300 FS	300	7027804
RKD 400 FS	400	7027806
RKD 500 FS	500	7027808
RKD 600 FS	600	7027810

RKD 100 DD	100	7027840
RKD 200 DD	200	7027842
RKD 300 DD	300	7027844
RKD 400 DD	400	7027846
RKD 500 DD	500	7027848
RKD 600 DD	600	7027850



Straight connector, side height 60 mm

Type	Item no.
RLVK 60 FS	6067093
RLVK 60 FT	6067603



Double clamp for fastening fittings

Type	Item no.
DOP A2	6035998



Cover clamp

Type	Item no.
DK DRLU A2	6052810



Turn buckle

Type	Item no.
DRL H S FT	6065018
DRL H S A2	6065016



Barrier strip, height 45 mm

Type	Length mm	Item no.
TSG 45 FS	3000	6062033
TSG 45 DD	3000	6062321



Barrier strip, height 60 mm

Type	Length mm	Item no.
TSG 60 FS	3000	6062068
TSG 60 DD	3000	6062327



Adjustable connector

Type	Item no.
RGV 60 FS	7082010
RGV 60 FT	7082223



Barrier strip connector

Type	Length mm	Item no.
TSGV A2	3000	6067970



Edge protection strip

Type	For plate thickness mm	Item no.
KSB 2 PVC	1-2	6072909
KSB 4 PVC	1-4	6072895

Surfaces and areas of application:

- FS** Strip galvanisation, for use in internal areas
- DD** Double-dip galvanisation, for use in external areas
- F** Electro galvanisation, for use in external areas
- FT** Hot-dip galvanisation, for use in external areas
- V2A** Stainless steel, rustproof