Cast resin in a set

 \oplus

With T 60 junction box and terminal strip - T 60 hars

The cast resin is tested and certified to DIN VDE 0278-631-1

000

T 60 hars 2010 007

Quick, simple and safe!

Ð

IP 68

0000



Building Connections

Set of T 60 junction box and cast resin

Quick, simple and safe: The 2-component cast resin comes in a pack with a junction box of the T 60 type with plug-in seal and terminal strip and protects your electrical installation effectively against moisture and mechanical loads.

The cast resin hardens completely within an hour and can not be altered afterwards. Once it has been processed it complies with the demands of the protection class IP68.





Dimensions



All the T series junction boxes are UV-resistant. They are made of a thermoplastic polypropylene plastic with plug-in seals made of ethylene vinyl acetate (EVA). This plastic is soft, which means that it is malleable. This allows installation of cables through the 7 x M25 seals, or the seals can be cut with a knife at the pre-marked points, in order to create an insertion opening for cables or pipes. Alternatively, instead of seals, cable glands can be inserted through the openings and be countered internally with a locknut.

The junction boxes can be mounted on mounting plates in the openings on the floor using steel bolts 3.5×9.5 .

Clear internal dimensions: 100x100x48 mm

Cover with labelling panel and lead-sealed.							
Туре	Colour	Entries	Dimension LxWxH mm	Clear internal dimensions mm		.Weight kg/100 p	
T 60 hars	Light grey	7 x M25	114x114x57	100x100x48	1	64,000	2010007

PP Polypropylene

OBO Bettermann Holding GmbH & Co. KG P.O. Box 1120 58694 Menden GERMANY Customer Service Tel.: +49 (0)2373 89-1700 Fax: +49 (0)2373 89-1238 export@obo.de

www.obo-bettermann.com

