

Technical data sheet

MS4121 mounting rail, slot 22 mm, A2, perforated

Item number: 1122929



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



A2	Stainless steel
2B	Bright, treated

Master data		
Item number	1122929	
Type	MS4121P6000A2	
Description 1	Profile rail	
Description 2	perforated, slot 22mm	
Manufacturer	OBO	
Dimension	6000x41x21	
Material	Stainless steel 1.4301	
Surface	Bright, treated	
Surface standard		
Smallest sales unit	6	
Unit of quantity	Metre	
Weight	140.95 kg	
Weight unit	kg/100 m	
CO2 Footprint (GWP) Cradle-to-Gate	7,2924 kg CO2e / 1 Meter	


Technical data sheet

MS4121 mounting rail, slot 22 mm, A2, perforated

Item number: 1122929



Dimensions



Length	6,000 mm
Width	41 mm
Height	21 mm
Dimension L	6,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	no
Hole size	14x28
Material thickness	2 mm
With perforation	yes
With toothing	yes
Profile shape	C profile
ROHS-conformant	yes
Slot width	22 mm
Static value A	1.65 cm ²
Static value I _y	0.95 cm ⁴
Static value I _z	4.51 cm ⁴
Static value W _y	0.89 cm ³
Static value W _z	2.2 cm ³