

Technical data sheet

Clamp clips, BBS clip for flat iron

Item number: 1171895



Suitable for flat, angular and U irons of 4–12 mm material thickness.

Clip and bolt made of hot-dip galvanised steel.

Polypropylene pressure sleeve, halogen-free, colour light grey RAL 7035.

Version with welding and/or locknuts for use under difficult circumstances and for vibration protection on request.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	1171895
Type	2056F 29 FT
Description 1	Clamp clip
Manufacturer	OBO
Dimension	29mm
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	100
Unit of quantity	Piece
Weight	3.2 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0721 kg CO2e / 1 Piece


Technical data sheet

Clamp clips, BBS clip for flat iron

Item number: 1171895



Dimensions



Dimension A	22.5 mm
Dimension B	29 mm
Dimension C	27 mm
Dimension E	16 mm
Dimension G (mm)	M6
Dimension H	59 mm
Dimension L	30.5 mm
Dimension t	1.5 mm
Dimension x	8.5 mm

Technical data

Halogen-free	yes
With plastic trough	yes
With metal trough	no
ROHS-conformant	yes
Impact-resistant	no
Clamping range D, max.	29 mm
Clamping range D, min.	22 mm
With counter-trough	no
Material of trough	Plastic
Material quality of trough	Polypropylene