

# Technical data sheet

## Clamp clip 2056 N-foot, 1-fold, metal pressure sleeve, A2

Item number: 1188374



Clamp clip with N-foot, metal pressure sleeve with rounded edges to protect the cable. For vertical and horizontal mounting of 1 single cable on a C-profile rail. For slot width 11–12 mm With 1-start screw thread on pressure sleeve, universal hexagonal screw head WAF10, with slot and cross recess. Suitable for assembly indoors and outdoors. We recommend the use of a counter-sleeve.



**A2** Stainless steel

**2B** Bright, treated

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 1188374                  |
| Type                               | BS-N1-M-16 A2            |
| Description 1                      | Clamp clip 2056          |
| Manufacturer                       | OBO                      |
| Dimension                          | 12-16mm                  |
| Material                           | Stainless steel 1.4301   |
| Surface                            | Bright, treated          |
| Surface standard                   |                          |
| Smallest sales unit                | 25                       |
| Unit of quantity                   | Piece                    |
| Weight                             | 3.523 kg                 |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,2268 kg CO2e / 1 Piece |


# Technical data sheet

Clamp clip 2056 N-foot, 1-fold, metal pressure sleeve, A2

Item number: 1188374



## Dimensions



|                  |         |
|------------------|---------|
| Length           | 22.5 mm |
| Width            | 20 mm   |
| Height           | 39 mm   |
| Plate thickness  | 1.5 mm  |
| Dimension A      | 22.5 mm |
| Dimension B      | 20 mm   |
| Dimension C      | 28 mm   |
| Dimension G (mm) | M6      |
| Dimension H      | 39 mm   |
| Dimension L      | 34 mm   |
| Dimension t      | 1.5 mm  |

## Technical data

|                                                |                 |
|------------------------------------------------|-----------------|
| Number of cables/pipes                         | 1               |
| For pipe diameter, max.                        | 16 mm           |
| For pipe diameter, min.                        | 12 mm           |
| for rail with slot width (with interval), max. | 12 mm           |
| for rail with slot width (with interval), min. | 11 mm           |
| Thread                                         | M6              |
| Halogen-free                                   | yes             |
| Length of external dimensions                  | 28 mm           |
| Max. Tightening torque                         | 3 Nm            |
| With plastic trough                            | no              |
| With metal trough                              | yes             |
| Mounting type                                  | Profile rail    |
| Slot width                                     | 10 mm           |
| Clamping range D, max.                         | 16 mm           |
| Clamping range D, min.                         | 12 mm           |
| Surface addition                               | Untreated       |
| Material addition                              | Rustproof steel |