

# Technical data sheet

## Adapter expansion M - PG

Item number: 2088318



The areas of application for brass cable glands range from junction boxes as a distribution/connection box up to large industrial applications for safe floor routing to switchgear cabinets with a control and distribution function. For high mechanical requirements, OBO can offer the entire family with long and short connection threads and locknuts with a metric and Pg thread.

CE M Pg

CuZn  
37

Brass

N

Nickel-plated

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 2088318                  |
| Type                               | 165 ADA M20-PG16         |
| Description 1                      | Adapter                  |
| Description 2                      | M - PG                   |
| Manufacturer                       | OBO                      |
| Dimension                          | M20-PG16                 |
| Material                           | Brass                    |
| Surface                            | Nickel-plated            |
| Surface standard                   |                          |
| Smallest sales unit                | 20                       |
| Unit of quantity                   | Piece                    |
| Weight                             | 1.65 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,0461 kg CO2e / 1 Piece |


# Technical data sheet

## Adapter expansion M - PG

Item number: 2088318



### Dimensions



|              |         |
|--------------|---------|
| Dimension D  | 24 mm   |
| Dimension L  | 19.5 mm |
| Dimension L1 | 6 mm    |
| Dimension L2 | 13.5 mm |

### Technical data

|                                    |        |
|------------------------------------|--------|
| explosion-proof                    | no     |
| Thread type: External thread       | Metric |
| Thread type: Internal thread       | PG     |
| Thread dimension, metric, external | 20     |
| Thread dimension, PG, internal     | 16     |
| ROHS-conformant                    | Exempt |
| Nickel-plated                      | yes    |