

Technical data sheet

Spreading anchor, plastic

Item number: 2347720



Nylon spreading anchor for mounting components on walls and ceilings. Suitable for solid building materials such as concrete, sand-lime brick and masonry. With pre-fixing of the screw for easy overhead mounting. The given load values are valid for wood screws with the specified diameter.



PA Polyamide

Master data

Item number	2347720
Type	SX Plus 5x25
Description 1	Spreading anchor
Manufacturer	OBO
Dimension	5x25
Colour	Light grey
Material	Polyamide
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.037 kg
Weight unit	kg/100 pc.


Technical data sheet

Spreading anchor, plastic

Item number: 2347720



Dimensions



Length	25 mm
Dimension D	5 mm
Dimension L	25 mm

Technical data sheet

Spreading anchor, plastic

Item number: 2347720



Technical data

Version for	Spreading anchor
Concrete Frat	350
Drill hole depth	35 mm
Drill hole diameter, max.	5 mm
Drill hole diameter, min.	5 mm
Suitable for fastening with cable ties	no
Suitable for gas concrete	yes
Suitable for screw diameter, max.	4 mm
Suitable for screw diameter, min.	3 mm
Suitable for hexagonal wood screw	yes
Hollow brick Hlz12 Frat	130
Porous calcareous sandstone KSL12 Fempf.	250
Solid calcareous sandstone KSL12 Frat	350
With edge	yes
With bolts	no
Porous concrete P2 Fempf.	30
Porous concrete P4 Fempf.	150
ROHS-conformant	yes
Full brick Mz12 Frat	270
Suitable for material	Calcareous sandstone Porous concrete Concrete Gas concrete Plasterboard Full brick Hollow brick
Mounting type, anchor, tie	Push-through mounting Pre-mounting