

Technical data sheet

Spreading anchor, plastic

Item number: 2347732



Nylon spreading anchor for mounting components on walls and ceilings. Suitable for solid building materials such as concrete, sand-lime brick and masonry. With pre-fixing of the screw for easy overhead mounting. The given load values are valid for wood screws with the specified diameter.



PA Polyamide

Master data		
Item number	2347732	
Type	SX Plus 12x60	
Description 1	Spreading anchor	
Manufacturer	OBO	
Dimension	12x60	
Colour	Light grey	
Material	Polyamide	
Smallest sales unit	25	
Unit of quantity	Piece	
Weight	0.449 kg	
Weight unit	kg/100 pc.	


Technical data sheet

Spreading anchor, plastic

Item number: 2347732



Dimensions



Length	60 mm
Dimension D	12 mm
Dimension L	60 mm

Technical data sheet

Spreading anchor, plastic

Item number: 2347732



Technical data

Version for	Spreading anchor
Concrete Frat	2400
Drill hole depth	80 mm
Drill hole diameter, max.	12 mm
Drill hole diameter, min.	12 mm
Suitable for fastening with cable ties	no
Suitable for gas concrete	yes
Suitable for screw diameter, max.	10 mm
Suitable for screw diameter, min.	8 mm
Suitable for hexagonal wood screw	yes
Hollow brick Hlz12 Frat	350
Porous calcareous sandstone KSL12 Fempf.	700
Solid calcareous sandstone KSL12 Frat	2400
With edge	yes
With bolts	no
Porous concrete P2 Fempf.	220
Porous concrete P4 Fempf.	800
Full brick Mz12 Frat	1250
Suitable for material	Calcareous sandstone Porous concrete Concrete Gas concrete Plasterboard Full brick Hollow brick
Mounting type, anchor, tie	Push-through mounting Pre-mounting