

Technical data sheet

Push-fit plug Delta-Push® with M6 thread

Item number: 2351673



Push-fit plug Delta-Push® for mounting electrical installations. Suitable for concrete, calcareous limestone, full brick, hollow brick and porous concrete. Toolless mounting by pushing into a drill hole in a wall or on a ceiling. Without screws. With M6 thread for screwing on Quick clips, for example.

HALOGEN
FREE

Ø6

PA

Polyamide

Master data

Item number	2351673
Type	DP GM6 30
Description 1	Push-fit plug
Description 2	with M6 thread
Available from	01.02.2025
Manufacturer	OBO
Dimension	39,0x10,0x10,0
Material	Polyamide
Smallest sales unit	100
Unit of quantity	Piece
Weight	0.072 kg
Weight unit	kg/100 pc.


Technical data sheet

Push-fit plug Delta-Push® with M6 thread

Item number: 2351673



Dimensions



Length 30 mm

Technical data

Version for	Push-fit anchor
Drill hole depth	35 mm
Drill hole diameter, max.	6 mm
Drill hole diameter, min.	6 mm
Suitable for fastening with cable ties	no
Suitable for gas concrete	yes
Suitable for hexagonal wood screw	no
Halogen-free	yes
With edge	yes
With bolts	no
Mounting temperature, max.	60 °C
Min. mounting temperature	5 °C
ROHS-conformant	yes
Temperature-resistance, max.	60 °C
Temperature resistance, min.	-20 °C
Suitable for material	Calcareous sandstone Porous concrete Concrete Gas concrete Full brick Hollow brick
Mounting type, anchor, tie	Pre-mounting

Loads

Breaking load lime sandstone	400 N
Safe working load concrete	175 N
Safe working load vertically perforated brick	130 N
Safe working load lime sandstone	175 N
Breaking load concrete	400 N
Breaking load vertically perforated brick	300 N