


Technical data sheet

Hexagonal bolt DIN 933 V2A

Item number: 3156044



Hexagonal bolt according to DIN 933 with metric thread.



A2	Stainless steel
2B	Bright, treated

Master data

Item number	3156044
Type	HHS M16x50 A2
Description 1	Hexagonal screw
Description 2	fully threaded
Manufacturer	OBO
Dimension	M16x50mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	50
Unit of quantity	Piece
Weight	10.3 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,4909 kg CO2e / 1 Piece


Technical data sheet

Hexagonal bolt DIN 933 V2A

Item number: 3156044



Dimensions



Length	50 mm
Dimension D	16 mm
Dimension d	16 mm
Dimension L	50 mm

Technical data

Thread	M16
Thread metric	16
Thread type	Metric
Thread length	50 mm
Head shape	Hexagonal
With flange	no
With nut	no
With washer	no
ROHS-conformant	yes
WAF	24
Screw system	Hexagonal
Self-locking	no
Full thread	yes
Left thread	no