

Technical data sheet

MMS-plus SS 10x95 hexagonal tie, with pressed washer,
made of A4 stainless steel
Item number: 3498128



Stainless steel screw-in anchor for direct mounting without additional anchors in cracked and uncracked concrete and masonry. With hex head drive and pressed washer to accept large loads. Suitable for fastening suspended loads from suspended supports and wall brackets in wet rooms and in outdoor areas.

Construction product tested according to EAD and CE mark, with European Technical Assessment (ETA) and proof of suitability. Load-bearing capacities under fire loads proven up to fire resistance class R120.



A4 Stainless steel

Master data

Item number	3498128
Type	MMS+ SS 10x95 A4
Description 1	Hexagon head anchor
Description 2	with combined washer
Manufacturer	OBO
Dimension	10x95mm
Colour	stainless steel
Material	Stainless steel 1.4401
Smallest sales unit	25
Unit of quantity	Piece
Weight	4.6 kg
Weight unit	kg/100 pc.


Technical data sheet

MMS-plus SS 10x95 hexagonal tie, with pressed washer,
made of A4 stainless steel

Item number: 3498128



Dimensions



Dimension	10x95
Length	95 mm
Dimension L	95 mm

Technical data

Anchor/nail/bolt version	Spiral anchor
Drill hole depth	80 mm
Drill hole diameter, min.	8 mm
Hardened	yes
Thread	10
Thread diameter ST	10
Clamping strength	35 mm
Head diameter	19 mm
Head shape	Hexagonal
ROHS-conformant	yes
WAF	13
Screw system	Hexagonal
Fire resistance class EN 13501-1	R30 R60 R90 R120