

Technical data sheet

Nail tie with nail head A5

Item number: 3499016



Nail tie with nail head for the anchoring of, for example, fire protection products, mounting rails, metal clips, substructures made of wood and metal, etc. on walls and ceilings from cracked concrete in indoor and outdoor areas. To knock in with a hammer or rotary drill. When loads occur the nail tie spreads out automatically and anchors itself in the drill hole. Rustproof and highly corrosion-resistant. Fire-safety tested, fire protection class R 120 according to European Technical Assessment ETA-06/0175.




A5 Stainless steel

Master data

Item number	3499016
Type	FNAII 6x30/5A5
Description 1	Nail anchor
Description 2	with nailhead
Manufacturer	OBO
Dimension	6x42,5
Colour	stainless steel
Material	Stainless steel
Smallest sales unit	50
Unit of quantity	Piece
Weight	1.065 kg
Weight unit	kg/100 pc.

Dimensions



Length	42.5 mm
Dimension L	42.5 mm

Technical data sheet

Nail tie with nail head A5

Item number: 3499016



Technical data

Version for	Lightning strike
Fastening unit	Miscellaneous
Drill hole depth	45 mm
Drill hole diameter, min.	6 mm
Clamping strength	5 mm
ROHS-conformant	yes
Self-drilling	no
Approvals available	yes
Suitable for material	Calcareous sandstone Concrete Natural stone
Mounting type, anchor, tie	Push-through mounting