

Technical data sheet

Round cable terminal to 25 mm² for 1801 VDE

Item number: 5015758



- For single or multi-wire cables 2.5–25 mm²
- For fine-wire cables to 16 mm² (max. Ø 7 mm)
- 1 division unit
- Lightning current carrying capacity 100 kA (10/350)
- Electrogalvanised steel
- Tension clamp with screw lock against self-loosening (e.g. required in industry and in explosion-protected areas)



St

Steel

G

Electrogalvanised

Master data

Item number	5015758
Type	1801 RK25
Description 1	Series terminal
Description 2	for equipotential busbar
Manufacturer	OBO
Dimension	25mm ²
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	10
Unit of quantity	Piece
Weight	1.323 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0439 kg CO2e / 1 Piece


Technical data sheet

Round cable terminal to 25 mm² for 1801 VDE

Item number: 5015758



Dimensions



Width 12 mm

Technical data

Connection options	2.5-25 mm ²
Suitable for ribbon conductor connection	no
Suitable for round cable connection	yes
Suitable for sector conductor connection	no
Max. Conductor cross-section	25 mm ²
ROHS-conformant	yes
Dividing unit TE (10 mm)	1
Suitable for busbar	Other