

Technical data sheet

Cable bracket Rd 8–10 mm with pre-mounted wood screw

Item number: 5207878



- With female thread M8 for screwing and through hole for wood screws
- For round conductor Rd 8-10
- Weather and temperature-resistant from -35 °C to +90 °C
- With pre-mounted wood screws (5 x 60) and plastic dowels (8 x 40)

PA Polyamide

Master data

Item number	5207878
Type	177 B-HD30
Description 1	Cable fixing device
Description 2	with wood screw
Manufacturer	OBO
Dimension	8-10 mm
Colour	Grey
Material	Polyamide
Smallest sales unit	50
Unit of quantity	Piece
Weight	1.503 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0597 kg CO2e / 1 Piece


Technical data sheet

Cable bracket Rd 8–10 mm with pre-mounted wood screw

Item number: 5207878



Dimensions



Length	22 mm
--------	-------

Technical data

Holder fastening type	Drill hole with M-thread
Conductor fastening type	With clamp clip
Thread metric	8
High voltage-resistant, insulated version	no
Cable dimensions	8–10 mm round
Mounting height	30 mm
Fit	Rd 8-10 mm
ROHS-conformant	yes
Material of the holder	Polyamide
Material of the base	Polyamide
Material of the crossbar	Polyamide