

# Technical data sheet

165 MBG... roof cable holder for flat roofs, black, with concrete

Item number: 5218704



- Closed form with base
- With double conductor holder
- Filling weight 1 kg (frost-resistant concrete)
- Sleeve made of polyethylene, black, UV-resistant and weather-resistant
- Base made of polyamide PA 6, black, UV-resistant and weather-resistant
- Base can be used on almost all roofing felt systems (bitumen, PVC)
- Types 165 MBG...FO: Packed in foil bag

PA/  
PE

Polyamide/Polyethylene

## Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 5218704                  |
| Type                               | 165 MBG-8-10 FO          |
| Description 1                      | Roof conductor holder    |
| Description 2                      | for flat roofs           |
| Manufacturer                       | OBO                      |
| Dimension                          | 8-10mm                   |
| Colour                             | Black                    |
| Material                           | Polyamide/Polyethylene   |
| Smallest sales unit                | 12                       |
| Unit of quantity                   | Piece                    |
| Weight                             | 100 kg                   |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,5082 kg CO2e / 1 Piece |


# Technical data sheet

165 MBG... roof cable holder for flat roofs, black, with concrete


Item number: 5218704



## Dimensions



|        |          |
|--------|----------|
| Length | 133.5 mm |
|--------|----------|



## Technical data

|                          |               |
|--------------------------|---------------|
| Application              | Flat roof     |
| Conductor fastening type | With clip     |
| Conductor diameter, max. | 10            |
| Conductor diameter, min. | 8             |
| Mounting type            | Miscellaneous |
| Fit                      | Rd 8-10 mm    |
| ROHS-conformant          | yes           |
| Clamping range D, max.   | 10 mm         |
| Clamping range D, min.   | 8 mm          |
| Material of the holder   | Plastic       |
| Material of the support  | Concrete      |