

# Technical data sheet

## Wire cable clamp A4

Item number: 5302188



Wire cable clamp, formerly DIN 741, for fastening steel wire tensioning ropes. The bracket of the wire rope clamp must be positioned over the unloaded end of the wire rope loop; the clamping body rests against the load-bearing, continuous section of the wire rope loop. To ensure a secure connection, at least 3 wire cable clamps are required per wire rope loop, spaced at intervals of 1–2 times the clamp width. The hexagonal nuts must be tightened evenly in alternating order and retightened after the rope has been loaded for the first time.



|    |                 |
|----|-----------------|
| A4 | Stainless steel |
| 2B | Bright, treated |

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 5302188                  |
| Type                               | 947 10 A4                |
| Description 1                      | Wire cable clamp         |
| Manufacturer                       | OBO                      |
| Dimension                          | 10mm                     |
| Material                           | Stainless steel 1.4401   |
| Surface                            | Bright, treated          |
| Surface standard                   |                          |
| Smallest sales unit                | 10                       |
| Unit of quantity                   | Piece                    |
| Weight                             | 6.31 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,3045 kg CO2e / 1 Piece |


# Technical data sheet

## Wire cable clamp A4

Item number: 5302188



### Dimensions



|             |       |
|-------------|-------|
| Dimension A | 42 mm |
| Dimension B | 11 mm |
| Dimension C | 8 mm  |

### Technical data

|                          |               |
|--------------------------|---------------|
| Version for              | Not insulated |
| for cable diameter, min. | 10 mm         |
| ROHS-conformant          | yes           |