


Technical data sheet

Folding and construction clamp, 12 mm

Item number: 5304407



- Flange thickness to 12 mm
- With pre-mounted fix contact clamping screw 5000
- 2 hexagonal bolts M8 x 20, bolts made of hot galvanised steel
- Terminal block made of malleable iron, hot galvanised
- Mounting of the round conductors either vertical or transverse to structure
- Corresponds to the requirements of DIN VDE 0185-305-3



SG

Cast steel

FT

Hot-dip galvanised

Master data

Item number	5304407
Type	5004 DIN-FT 12
Description 1	Folding clamp
Description 2	fix contact
Manufacturer	OBO
Dimension	12mm
Material	Cast steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	10
Unit of quantity	Piece
Weight	18.73 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,5329 kg CO2e / 1 Piece



Technical data sheet

Folding and construction clamp, 12 mm

Item number: 5304407



Dimensions



Length	55 mm
Width	35 mm
Dimension L	55 mm
Dimension t	20 mm

Technical data

Type of fastening screw	Clamping screw
Type of connector	Clamp connector
Lightning current carrying capacity	N/50 kA
Suitable for connection	Miscellaneous
Fit	Rd 8-10 mm
ROHS-conformant	yes
Intermediate plate	no
Clamping range, max.	12 mm