


Technical data sheet

T connector Rd 8–10 mm Cu

Item number: 5311152



- With 2 hexagonal bolts M6 x 16 (VA)
- Complies with the requirements of VDE 0185-305-3 (IEC/ EN 62305-3)



Cu Copper

Master data		
Item number	5311152	
Type	245 8-10 CU	
Description 1	T-connector	
Manufacturer	OBO	
Dimension	8-10mm	
Material	Copper	
Smallest sales unit	10	
Unit of quantity	Piece	
Weight	11.56 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,3284 kg CO2e / 1 Piece	


Technical data sheet

T connector Rd 8–10 mm Cu

Item number: 5311152



Dimensions



Technical data

Type of fastening screw	Hexagonal bolt
Type of connector	T connector
Lightning current carrying capacity	N/50 kA
Suitable for connection	Round conductor Rd 8–10 / Rd 8–10
Fit	Rd 8-10 mm
ROHS-conformant	yes
Intermediate plate	no