

# Technical data sheet

Quick connector, upper part Rd 8–10 mm

Item number: 5311503



- For round conductor fastening RD 8-10
- Suitable for M10 bolts



St

Steel

FT

Hot-dip galvanised

## Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 5311503                  |
| Type                               | 249 8-10 ST-OT           |
| Description 1                      | Quick connector          |
| Description 2                      | cover                    |
| Manufacturer                       | OBO                      |
| Dimension                          | 40x40mm                  |
| Material                           | Steel                    |
| Surface                            | Hot-dip galvanised       |
| Surface standard                   | DIN EN ISO 1461          |
| Smallest sales unit                | 100                      |
| Unit of quantity                   | Piece                    |
| Weight                             | 3.24 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,1077 kg CO2e / 1 Piece |


# Technical data sheet

Quick connector, upper part Rd 8–10 mm

Item number: 5311503



## Dimensions



|             |       |
|-------------|-------|
| Dimension A | 40 mm |
|-------------|-------|

## Technical data

|                 |            |
|-----------------|------------|
| Fit             | Rd 8-10 mm |
| ROHS-conformant | yes        |