


Technical data sheet

Folding clamp and connection terminal up to 5 mm FT plate thickness

Item number: 5317428



- Plate thickness to 5 mm
- For cable routing along and across the plate
- 4 hexagonal bolts M6 x 16
- Meets the requirements of VDE 0185-305 (IEC 62305)



St

Steel

FT

Hot-dip galvanised

Master data

Item number	5317428
Type	274 FT
Description 1	Folding clamp
Manufacturer	OBO
Dimension	8mm
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	20
Unit of quantity	Piece
Weight	10.4 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,3872 kg CO2e / 1 Piece


Technical data sheet

Folding clamp and connection terminal up to 5 mm FT plate thickness

Item number: 5317428



Dimensions



Length	66 mm
Width	40 mm

Technical data

Type of fastening screw	Hexagonal bolt
Type of connector	Folding clamp
Lightning current carrying capacity	N/50 kA
Fit	Rd 8 mm
ROHS-conformant	yes
Clamping range, max.	5 mm