


Technical data sheet

Separating piece for Rd 8–10 and FL 30–40 mm

Item number: 5336457



- Fit: Rd 8-10 x FL 30-40
- With 2 hexagonal bolts M8 x 20 (VA)



A2 Stainless steel

Master data

Item number	5336457
Type	233 A VA
Description 1	Separating piece
Manufacturer	OBO
Dimension	FL30-40/8-10
Material	Stainless steel 1.4301
Smallest sales unit	10
Unit of quantity	Piece
Weight	7.851 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,4973 kg CO2e / 1 Piece


Technical data sheet

Separating piece for Rd 8–10 and FL 30–40 mm

Item number: 5336457



Dimensions



Technical data

Suitable for connection	Round conductor Rd 8-10 / flat conductor FI 30-40
Fit	Rd 8-10/FL30-40 mm
ROHS-conformant	yes
Bimetal connector	no
Intermediate plate	no