


Technical data sheet

Insulated air-termination rod for inner-routed isCon® conductor with side exit

Item number: 5408878



- For routing the OBO isCon® conductors in pipes
- With cable outlet to the side, matching the isFang air-termination stand with outlet to the side, type isFang 3B-A
- Suitable for wind loads according to Eurocode 1: DIN EN 1991-1-4
- Tested according to VDE V 0185-561-8 (IEC TS 62561-8)
- Stand pipe and interception tip made from aluminium
- Middle piece made from glass-fibre reinforced plastic (GFK)



GFK Fibre-glass-reinforced plastic

Master data

Item number	5408878
Type	isFang IN-A L8
Description 1	Insul. interception rod+outlet
Description 2	for isCon conductor, internal
Manufacturer	OBO
Dimension	8000mm
Material	Fibre-glass-reinforced plastic
Smallest sales unit	1
Unit of quantity	Piece
Weight	1385.741 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	128,2923 kg CO2e / 1 Piece


Technical data sheet

Insulated air-termination rod for inner-routed isCon® conductor with side exit

Item number: 5408878



Dimensions



Length	8,000 mm
Dimension A	5,335 mm
Dimension B	1,000 mm
Dimension d min.	50 mm
Dimension H	1,500 mm
Dimension L	8,000 mm

Technical data

Connection	Round conductor
Version for	Air-termination rod
High voltage-resistant, insulated version	yes
ROHS-conformant	yes