


Technical data sheet

Rung WSK 40

Item number: 6008046



Angle profile rungs for use in heavy-duty vertical ladders and in IS 8 supports.
The maximum rung load is 250 kg.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	6008046
Type	WSK 40 40 FT
Description 1	Angle rung
Description 2	for IS 8 support
Manufacturer	OBO
Dimension	B354mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	122 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	2,8691 kg CO2e / 1 Piece


Technical data sheet

Rung WSK 40

Item number: 6008046



Dimensions



lampDimension WxH	40 x 40 mm
Length	354 mm
Width	354 mm
Height	100 mm

Technical data

Material thickness	4 mm
ROHS-conformant	yes