

Technical data sheet

End piece, trunking type WDK 60090

Item number: 6022502



End piece to close the WDK trunking.
The end pieces are pushed onto the trunking and kept in place by the spring action.



PVC Polyvinylchloride

Master data

Item number	6022502
Type	WDK HE60090GR
Description 1	End piece
Manufacturer	OBO
Dimension	60x90mm
Colour	Stone grey; RAL 7030
Material	Polyvinylchloride
Smallest sales unit	10
Unit of quantity	Piece
Weight	2.337 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0808 kg CO2e / 1 Piece


Technical data sheet

End piece, trunking type WDK 60090

Item number: 6022502



Dimensions



Length	27.5 mm
Width	90 mm
Height	60 mm
Dimension a	90 mm
Dimension b	60 mm
Dimension H	90 mm

Technical data

Version for	Left/right
Fastening type	Lockable
Maintain electrical functions	no
Halogen-free	no
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C