

Technical data sheet

Trunking, type WDK 80170

Item number: 6027229



Wall installation trunking as trunking base with base perforation and matching trunking cover.
Four cover fixing devices included.
Lid clamp can be moved along the entire length of the trunking.



PVC Polyvinylchloride

Master data

Item number	6027229
Type	WDK80170LGR
Description 1	Wall trunking system
Description 2	with base perforation
Manufacturer	OBO
Dimension	80x170x2000
Colour	Light grey; RAL 7035
Material	Polyvinylchloride
Smallest sales unit	8
Unit of quantity	Metre
Weight	214 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	4,4472 kg CO2e / 1 Meter


Technical data sheet

Trunking, type WDK 80170

Item number: 6027229



Dimensions



Length	2,000 mm
Width	170 mm
Height	80 mm

Technical data

Number of fixed partitions	0
Number of cables NYM 3 x 1.5 mm ² Ø 10.5 mm (without socket)	64
Number of cables NYM 3 x 2.5 mm ² Ø 11.5 mm (without socket)	53
Number of cables NYM 5 x 1.5 mm ² Ø 12.0 mm (without socket)	49
Number of insertable partitions	2
Version, cable trunking cover	Loose
Fastening type	Base perforation
Maintain electrical functions	no
Halogen-free	no
Cable retaining clip	yes
Duct connector	no
Delivery on a roll	no
Usable cross-section	11108 mm ²
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK04
Permitted temperature range, max.	60 °C
Permitted temperature range, min.	-5 °C